

a Garlock Hygienic Technologies company

Gasket Color Coding

Many sanitary elastomeric materials are the same in appearance. Rubber Fab sanitary gaskets are specifically color coded with dots to easily identify the gasket material. Please refer to the chart below to visually identify each material.





Material	Dot Description	Color Code
Tuf-Steel®	no dot	
Tuf-Flex [®]	no dot	
PTFE	no dot	
PTFE - Type III Envelope Style with FKM Fluoroelastomer Filler	one white dot & one yellow dot	\bigcirc
PTFE - Type III Envelope Style with EPDM Filler	three green dots	
FKM Fluoroelastomer	one white dot & one yellow dot	\bigcirc
EPDM - peroxide cured	three green dots	
Silicone - white platinum	one pink dot if requested	\bigcirc
Silicone - platinum cured	no dot	
Buna	one red dot	
Detectomer [®] Metal Detectable	one blue dot	The blue dot is added to the dot of the elastomer
Detectomer® Metal Detectable/ X-ray Inspectable	two blue dots	The blue dots are added to the dot of the elastomer

ı.

Detectomer[®] Example: EPDM Metal Detectable/X-ray Inspectable would have two blue dots and three green dots. Tuf-Steel[®], Tuf-Flex[®], and Detectomer[®] are registered trademarks of Rubber Fab

Distributed by:



7033 Telford Way #20, Mississauga, ON L5S 1V4 Tel: **905.677.9000 •** Toll Free: **1.800.486.7863** www.tricanada.com